

| assessment_id | sale_id | Vacant_Improved | ASR |
|-----------------|---------|-----------------|------|
| 367ST-505001300 | 1527659 | Vacant | 1.38 |
| 370FU-505001900 | 2209811 | Vacant | 1.32 |
| 370FU-505001950 | 2209812 | Vacant | 1.32 |
| 370FU-505002000 | 2209813 | Vacant | 1.65 |
| 397AL-505001650 | 2240561 | Vacant | 0.80 |
| 400-000230100 | 2012690 | Improved | 2.03 |
| 400-000301101 | 2237579 | Improved | 0.87 |
| 400-000306301 | 1514170 | Improved | 1.05 |
| 400-000308333 | 2042430 | Improved | 0.98 |
| 400-000325301 | 1524204 | Improved | 0.74 |
| 400-000607200 | 1525546 | Improved | 0.89 |
| 400-000719101 | 1052037 | Improved | 2.71 |
| 400-000920201 | 2078990 | Improved | 1.27 |
| 400-001110400 | 2219970 | Improved | 0.87 |
| 400HO-606000050 | 993923 | Vacant | 1.16 |
| 400HO-606000100 | 944642 | Vacant | 0.82 |
| 400HO-606000200 | 944644 | Vacant | 1.00 |
| 400HO-606000250 | 941940 | Vacant | 1.30 |
| 400HO-606000300 | 1555299 | Vacant | 0.69 |
| 400HO-606000350 | 1556772 | Vacant | 0.60 |
| 400HO-606000400 | 941943 | Vacant | 1.24 |
| 400HO-606000500 | 993924 | Vacant | 3.63 |
| 400HO-606000550 | 958390 | Vacant | 0.94 |
| 400HO-606000600 | 1513173 | Vacant | 3.63 |
| 400HO-606000800 | 818393 | Vacant | |
| 400HO-606000850 | 942586 | Vacant | 0.81 |
| 400HO-606001000 | 2223711 | Vacant | 0.88 |
| 400HO-606001050 | 993925 | Vacant | |
| 400HO-606001100 | 990163 | Vacant | |
| 400HO-606001150 | 1573145 | Vacant | 1.13 |
| 400HO-606001200 | 993926 | Vacant | |
| 400HO-606001250 | 993927 | Vacant | |
| 400HO-606001300 | 1020059 | Vacant | |
| 400HO-606001350 | 993928 | Vacant | |
| 400HO-606001400 | 1046497 | Vacant | |
| 400HO-606001450 | 1024864 | Vacant | |
| 400HO-606001500 | 993930 | Vacant | |
| 400HO-606001550 | 993931 | Vacant | |
| 400HO-606001600 | 993932 | Vacant | |
| 400HO-606001650 | 993933 | Vacant | |
| 400HO-606001700 | 993934 | Vacant | |
| 400HO-606002200 | 2231065 | Vacant | 0.71 |
| 400HO-606002250 | 1512279 | Vacant | 1.47 |
| 400LU-404000100 | 1531521 | Vacant | 1.00 |
| 400LU-404000150 | 2083105 | Vacant | 0.96 |
| 400LU-404000250 | 1008425 | Vacant | 0.85 |
| 400LU-404000350 | 1014429 | Vacant | 0.85 |
| 400LU-404000450 | 1518647 | Vacant | 0.85 |
| 400LU-404000550 | 1030133 | Vacant | 0.81 |
| 400LU-404000600 | 1030956 | Vacant | 0.77 |
| 400LU-404000650 | 1030958 | Vacant | 1.00 |
| 400LU-404000700 | 1020017 | Vacant | 0.82 |

| | | | |
|-----------------|---------|----------|------|
| 400LU-404000750 | 2214708 | Improved | 1.24 |
| 400LU-404000800 | 924025 | Vacant | 0.98 |
| 400LU-404000850 | 924026 | Vacant | 0.89 |
| 400LU-404000950 | 1579275 | Vacant | 1.15 |
| 400LU-404001200 | 1539406 | Improved | 0.83 |
| 400LU-404001350 | 1004813 | Vacant | 1.11 |
| 400LU-404001400 | 932631 | Vacant | 1.10 |
| 400LU-404001450 | 948991 | Vacant | 1.01 |
| 400LU-404001500 | 952906 | Vacant | 0.99 |
| 400LU-404001600 | 912639 | Vacant | 1.06 |
| 400LU-404001650 | 915563 | Vacant | 1.02 |
| 400LU-404001650 | 2076729 | Improved | 0.92 |
| 400LU-404002000 | 2092600 | Improved | 0.93 |
| 400LU-404002100 | 926394 | Vacant | 1.10 |
| 400LU-404002150 | 929286 | Vacant | 1.06 |
| 400LU-404002200 | 1579276 | Improved | 1.01 |
| 400LU-404002350 | 1580191 | Improved | 1.11 |
| 400LU-404002500 | 1001382 | Vacant | 1.12 |
| 400LU-404002520 | 961845 | Vacant | 0.81 |
| 400LU-404002530 | 1019052 | Vacant | 1.14 |
| 400LU-404003200 | 1527868 | Vacant | 1.04 |
| 400LU-404003250 | 1526000 | Vacant | 1.04 |
| 400LU-404003300 | 2231080 | Vacant | 0.98 |
| 400LU-404003450 | 1552647 | Vacant | 0.96 |
| 400LU-404003650 | 2079090 | Vacant | 1.02 |
| 400LU-404003800 | 1514201 | Vacant | 1.02 |
| 400LU-404003950 | 1576520 | Vacant | 1.17 |
| 400LU-404004100 | 2007142 | Improved | 0.59 |
| 400LU-404004350 | 1570891 | Vacant | 1.50 |
| 400LU-404004502 | 1526017 | Vacant | 1.06 |
| 400LU-404004504 | 1581728 | Vacant | 0.96 |
| 400LU-404004506 | 1506865 | Vacant | 0.86 |
| 400LU-404004508 | 2045368 | Vacant | 0.95 |
| 400LU-404004510 | 2115384 | Vacant | 0.82 |
| 400LU-404004512 | 1515326 | Vacant | 1.05 |
| 400LU-404004514 | 2079096 | Vacant | 0.86 |
| 400LU-404004518 | 1508026 | Vacant | 0.91 |
| 400LU-404004522 | 1504002 | Vacant | 1.15 |
| 400LU-404004524 | 2080709 | Vacant | 1.11 |
| 400LU-404004526 | 2023033 | Vacant | 1.00 |
| 400LU-404004528 | 2239395 | Improved | 0.68 |
| 400LU-404004530 | 1508027 | Vacant | 1.00 |
| 400LU-404004534 | 2017567 | Vacant | 0.95 |
| 400LU-404004536 | 2218978 | Vacant | 0.93 |
| 400LU-404004538 | 1576025 | Vacant | 0.89 |
| 400LU-404004600 | 1565289 | Vacant | 1.19 |
| 400LU-404004655 | 2159081 | Vacant | 1.26 |
| 400LU-404004660 | 1500836 | Vacant | 1.09 |
| 400LU-404004665 | 1552663 | Vacant | 0.86 |
| 400LU-404004670 | 1580913 | Vacant | 0.87 |
| 400LU-404004675 | 2102325 | Vacant | 1.01 |
| 400LU-404004680 | 1511243 | Vacant | 0.92 |
| 400LU-404004689 | 1560635 | Vacant | 0.86 |

| | | | |
|-----------------|---------|----------|------|
| 400LU-404004800 | 2030018 | Vacant | 0.81 |
| 400LU-505025018 | 1580074 | Vacant | 1.23 |
| 400LU-505025034 | 1575759 | Improved | 0.91 |
| 400LU-505025038 | 1513125 | Improved | 1.43 |
| 400LU-505025043 | 2220829 | Improved | 0.61 |
| 400LU-505025071 | 1512985 | Improved | 1.47 |
| 400LU-505025190 | 2217365 | Vacant | 1.25 |
| 400LU-505040250 | 2199635 | Vacant | 1.23 |
| 400RH-303000150 | 2083114 | Improved | 1.72 |
| 400RH-303000250 | 2213075 | Improved | 1.12 |
| 400RH-303000350 | 1524141 | Improved | 0.93 |
| 400RH-303000450 | 1524993 | Improved | 0.98 |
| 400RH-303001450 | 2201294 | Vacant | 0.73 |
| 400RH-303001550 | 2001922 | Vacant | 0.85 |
| 400RH-303002400 | 2016853 | Vacant | 1.25 |
| 400RH-303002550 | 1572402 | Vacant | 1.36 |
| 400RH-303002600 | 2216378 | Vacant | 1.11 |
| 400RH-303002700 | 2016854 | Vacant | 0.99 |
| 400SH-707000250 | 1035150 | Vacant | 1.07 |
| 400SH-707000300 | 946422 | Vacant | 0.94 |
| 400SH-707000550 | 2083136 | Vacant | 1.00 |
| 400SH-707001000 | 961836 | Vacant | 0.72 |
| 400SH-707001750 | 913850 | Vacant | 0.86 |
| 400SH-707001800 | 1034407 | Vacant | 1.07 |
| 400SH-707002150 | 878876 | Vacant | 1.17 |
| 426CR-505001300 | 1535836 | Vacant | 2.70 |
| 426CR-505001400 | 2022768 | Vacant | 0.37 |
| 426CR-505011050 | 1522762 | Vacant | 0.51 |
| 426CR-505012250 | 1575668 | Vacant | 0.31 |
| 428RE-505001050 | 1524834 | Vacant | 0.75 |
| 429ET-505002000 | 1521783 | Vacant | 0.12 |
| 430-000209100 | 2240565 | Improved | 1.08 |
| 430-000235201 | 1514176 | Improved | 1.26 |
| 430-000323100 | 1521867 | Improved | 1.60 |
| 430-000609201 | 2246193 | Improved | 1.00 |
| 430-000626401 | 2051717 | Improved | 0.86 |
| 430-000703201 | 1506483 | Improved | 1.01 |
| 430-001031301 | 2005079 | Improved | 1.09 |
| 430BA-767600250 | 2235787 | Improved | 1.22 |
| 430BA-767601200 | 2105209 | Improved | 1.04 |
| 430BA-767601750 | 1525890 | Improved | 0.96 |
| 430BA-767602950 | 1512169 | Improved | 0.85 |
| 430BA-767603050 | 2233345 | Improved | 1.38 |
| 430BA-767603700 | 2218358 | Improved | 0.92 |
| 430CR-505000450 | 2045159 | Vacant | 1.07 |
| 430CR-505000450 | 2228993 | Vacant | 0.40 |
| 430CR-505000600 | 2029767 | Vacant | 0.76 |
| 430CR-505003700 | 1573885 | Vacant | 0.57 |
| 430DI-252501090 | 2210258 | Improved | 1.05 |
| 430ME-202001700 | 2212861 | Vacant | 1.04 |
| 430RH-454500450 | 1524137 | Vacant | 1.00 |
| 430RH-454500700 | 2056832 | Improved | 1.20 |
| 430RH-454501500 | 2201964 | Vacant | 1.00 |

| | | | |
|-----------------|---------|----------|------|
| 430RH-454501550 | 2082460 | Vacant | 1.86 |
| 430RH-454506240 | 2083140 | Vacant | 1.03 |
| 430RH-454506250 | 2056863 | Vacant | 0.97 |
| 430RH-454509010 | 2197392 | Vacant | 0.63 |
| 430TW-404000700 | 2008015 | Vacant | 2.85 |
| 430TW-404001100 | 2233386 | Vacant | 0.93 |
| 430TW-404001700 | 1521879 | Vacant | 1.32 |
| 430TW-404001700 | 2215331 | Vacant | 1.51 |
| 430TW-404004300 | 1582463 | Vacant | 2.64 |
| 430TW-404004350 | 1582464 | Vacant | 2.64 |
| 430TW-404004400 | 1582465 | Vacant | 2.64 |
| 430TW-404005500 | 1515967 | Vacant | 1.01 |
| 430YC-353502550 | 2115328 | Vacant | 0.68 |
| 430YC-353503650 | 2233202 | Vacant | 1.45 |
| 430YC-353503950 | 2217076 | Vacant | 0.29 |
| 430YC-353504550 | 2233388 | Vacant | 1.19 |
| 430YC-353504650 | 2236914 | Vacant | 1.04 |
| 430YC-353505150 | 2239907 | Vacant | 0.94 |
| 430YC-353505250 | 2243149 | Vacant | 1.24 |
| 430YC-353505300 | 2250496 | Vacant | 1.24 |
| 430YC-353505400 | 2256050 | Vacant | 1.24 |
| 430YC-353505500 | 2247178 | Vacant | 1.56 |
| 430YC-353506200 | 1522073 | Vacant | 2.73 |
| 430YC-353506250 | 1524992 | Vacant | 2.00 |
| 430YC-353506400 | 1524985 | Vacant | 2.00 |
| 430YC-353510000 | 2233193 | Vacant | 3.03 |
| 430YC-363602300 | 2100056 | Vacant | 1.00 |
| 431-000404201 | 2173442 | Improved | 0.78 |
| 431-000621101 | 2100005 | Improved | 0.43 |
| 431-000710102 | 1568241 | Improved | 1.23 |
| 431-000716301 | 1053122 | Improved | 0.77 |
| 431-000731101 | 1580127 | Improved | 0.98 |
| 431-000802301 | 2007064 | Improved | 1.59 |
| 431-000807401 | 1578316 | Improved | 1.00 |
| 431-001206005 | 1569540 | Improved | 1.14 |
| 431-001206007 | 1513636 | Improved | 1.22 |
| 431-001211001 | 1518760 | Improved | 0.58 |
| 431-001502002 | 2082084 | Improved | 0.75 |
| 431-001812001 | 2219199 | Improved | 0.62 |
| 431DO-606003850 | 2227847 | Vacant | 2.20 |
| 431DO-606005100 | 2212923 | Vacant | 1.36 |
| 458FA-505006100 | 1573242 | Vacant | 0.19 |
| 458GR-505005600 | 2233289 | Vacant | 0.12 |
| 460BR-505002200 | 2092322 | Vacant | 0.76 |
| 460HA-505003750 | 2033440 | Vacant | 0.36 |
| 463MC-505002950 | 1571643 | Vacant | 0.21 |
| 463MC-505008900 | 2212603 | Vacant | 0.03 |
| 488GA-505001450 | 2214845 | Vacant | 0.63 |
| 488GA-505001900 | 2056665 | Vacant | 0.97 |
| 488GA-505002850 | 1525789 | Vacant | 2.36 |
| 488GA-505003200 | 2209137 | Vacant | 0.65 |
| 488SN-505000450 | 1049041 | Vacant | 0.33 |
| 520FO-404001800 | 1504928 | Vacant | 0.52 |

| | | | |
|-----------------|---------|--------|------|
| 520NO-505001400 | 1532235 | Vacant | 0.07 |
| 520NO-505002000 | 1047902 | Vacant | 0.04 |
| AYLSH-505000050 | 2225341 | Vacant | 1.34 |
| AYLSH-505002900 | 1519262 | Vacant | 3.24 |
| BEATT-505003150 | 1568022 | Vacant | 0.19 |
| LOVE-505001500 | 2182697 | Vacant | 1.07 |
| MEATH-404008550 | 1057091 | Vacant | 0.63 |
| MEATH-404008750 | 1532871 | Vacant | 0.08 |
| MISTA-505001600 | 1578192 | Vacant | 0.35 |
| MISTA-505005600 | 2223350 | Vacant | 0.33 |
| MISTA-505005700 | 2223351 | Vacant | 0.32 |
| PLEAS-505002600 | 2241957 | Vacant | 1.32 |
| PLEAS-505004750 | 1538144 | Vacant | 1.76 |
| SPALD-505008150 | 2015610 | Vacant | 0.42 |
| SPALD-505008200 | 2015611 | Vacant | 0.42 |
| SPALD-505008250 | 1520122 | Vacant | 1.06 |
| SPALD-505012900 | 1553975 | Vacant | 1.06 |
| SPALD-505012930 | 1553979 | Vacant | 1.06 |
| SPALD-505013250 | 1553981 | Vacant | 1.06 |
| STBEN-505000250 | 1541734 | Vacant | 2.26 |
| STBEN-505004950 | 1517556 | Vacant | 0.37 |
| WEIRD-505008100 | 1528943 | Vacant | 0.24 |
| WEIRD-505018650 | 2247813 | Vacant | 0.14 |
| ZENON-505001450 | 2099943 | Vacant | 1.08 |
| ZENON-505006900 | 2229254 | Vacant | 0.13 |